## **II TRACO POWER**


## **Common Mode Choke**

**TCK-076** 


Order Code	TCK-076
Inductance (each winding)	<b>55 μH ±35%</b> (at 100 kHz / 20 mV)
Impedance (DCR)	9 mΩ max.
Rated Current	5.7 A max.
Rated Voltage	500 VDC max. (between windings)
Operating Temperature	-40°C to +105°C
RoHS Exemptions	No Exemptions
Overview Link	www.tracopower.com/overview/tck-076



## Impedance Curve



## **Outline Dimensions**



Dimensions [mm]	
Α	11.5 max.
В	11.5 max.
С	8.8 max.
D	2.5 min.
E	7.62 ±0.2
F	7.62 ±0.2
G	ø 0.6 ±0.1

All specifications valid at +25°C, unless otherwise stated.

