

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME**
CB TEST CERTIFICATE

Product

Switching power supply

Name and address of the applicant

TRACO ELECTRONIC AG
SIHLBRUGGSTRASSE 111 CH-6340 BAAR,
SWITZERLAND

Name and address of the manufacturer

TRACO ELECTRONIC AG
SIHLBRUGGSTRASSE 111 CH-6340 BAAR,
SWITZERLAND

Name and address of the factory

TRACO ELECTRONIC AG
SIHLBRUGGSTRASSE 111 CH-6340 BAAR,
SWITZERLAND

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

☐ [Additional Information on page 2](#)

Input: 100-240 Vac, 50/60 Hz,
1.6 A max. for TPP100-XBYzzzzzzzz series,
2.0 A max. for TPP150-XBYzzzzzzzz series.

Output Rating: See test report for details.

Trademark (if any)

TRACO



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

TPP100-XBYzzzzzzzz, TPP150-XBYzzzzzzzz
See Page 2

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 60601-1: 2006 / A1: 2013 / A12: 2014;

☐ [Additional Information on page 2](#)

A sample of the product was tested and found to be in conformity with

IEC 60601-1(ed.3), IEC 60601-1(ed.3);am1

As shown in the Test Report Ref. No. which forms part of this Certificate

170102102 issued on 2017-03-30

This CB Test Certificate is issued by the National Certification Body



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2017-04-03

Signature:

Jan-Erik Storgaard

Model Details:

TPP100-XBYzzzzzzzz (X can be 112, 115, 124, 128, 136 and 148 or any other number within SELV limit; Y can be A, U, D or blank; z can be any alphanumeric or blank for marketing purpose and no impact safety related critical components and constructions)

TPP150-XBYzzzzzzzz (X can be 105, 112, 115, 124, 128, 136 and 148 or any other number within SELV limit; Y can be A, U, D or blank; z can be any alphanumeric or blank for marketing purpose and no impact safety related critical components and constructions)

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2017-04-03

Signature:



Jan-Erik Storgaard